

Rigid load arm, Base length in m / safe working load in t: 1,6/1



Order data

Order number	919973 1,6/1
GTIN	4052462012714
Item class	94B

Description

Version:

Load arms increase the reach of the fork-lift truck. Sturdy steel construction with fork insertion slots for fork tines. Also suitable for clamp trucks. Chain protection against accidental slippage and a swivel hook. Rigid design with 3 available hook positions.

Colour:

Optional **paint finishes** RAL 5012, Light blue, RAL 2000 Yellow orange, RAL 3000 Fire red, RAL 6011 Reseda green, RAL 7005 Mouse grey.

Note:

Comply with the load capacity of the fork lift truck!

Technical description

Width	600 mm
Base length	1600 mm
Internal dimension at intake: width	220 mm
Load capacity of the outermost eye	200 kg
maximum load capacity	1000 kg
Weight	42 kg
Internal dimension at intake: height	80 mm
Fork-lift fork socket pitch	160 mm
Colour selection	RAL 5012, 2000, 3000, 6011, 7005

Type of product

Load arm