

**LESSMANN®**  
THE GERMAN BRUSH COMPANY

## Knotted end brush Stainless steel wire, Brush Ø D1× bristle thickness: 28X0,35mm



### Order data

Order number	574900 28X0,35
GTIN	4017359039427
Item class	57L

### Description

#### Version:

Smooth, knotted wire, crimped into steel ferrule, **shank Ø 6 mm**, even density, extremely wear-resistant.

Stainless wire quality 1.4401 (AISI 316). Carrier body with plastic sheathing for machining stainless steel.

#### Application:

For deburring, removing paint, and for all moderate to heavy brushing jobs. **As speed increases the brush opens, this allows it to be introduced even into tight spaces**, e.g. when brushing the inside of casings.

### Technical description

Bristle thickness	0.35 mm
Number of twisted knots	12
Length of brush section H <sub>1</sub>	28 mm
maximum speed	20000 min <sup>-1</sup>
Brush Ø D <sub>1</sub>	28 mm
Shank Ø D <sub>s</sub>	6 mm
Brush material	Stainless steel wire

Twisted knotting	left-hand plait
Type of product	End brush