



Welder's mask, automatic 3M™ Speedglas™ 100 V, Colour: GRAPHIC



Order data

| | |
|--------------|----------------|
| Order number | 097910 GRAPHIC |
| GTIN | 4054596290587 |
| Item class | 040 |

Description

Version:

Automatic welding mask with all the important basic functions. For reliable protection at an **excellent price-performance ratio**. With **comfortable headband** and **free-moving ratchet system** for precise adjustment of the fit. Delay function for individual determination of the brightening delay. **Increased shock resistance** to EN 175:B. Compatible with other personal protective equipment, such as dust masks. Exchangeable visor. **Shade levels: 8 - 12. Shade level in the light state: 3.** With lithium 3 V battery (working life 1,500 hours). **Field of view of the welding filter: 44 × 93 mm.**

Application:

MIG/MAG welding, stick welding and high-Ampère TIG welding

Standard:

EN 175:B; EN 379; EN 166:BT

Switching time from bright to dark: 0.1 ms

Switching time from dark to bright: 40 - 250 ms

Classification to EN 379: 1 / 2 / 2 / 2

Technical description

| | |
|------------------------------------|--------|
| Switching time from bright to dark | 0.1 ms |
|------------------------------------|--------|

Data sheet

| | |
|---|-----------------|
| Classification to EN 379 | 1 / 2 / 2 / 2 |
| Switching time from dark to bright | 40 - 250 ms |
| Number of batteries contained | 1 |
| Article no of the battery / rechargeable battery fitted | 081560 CR2032 |
| Power supply | Battery-powered |
| Type of product | Welder's mask |