

## Handling lift table, Safe working load: 3000kg



### Order data

Order number	919992 3000
GTIN	4050939066239
Item class	08Y

### Description

#### Version:

Sturdy bracing struts with a platform made of smooth steel plate. For a wide range of applications, such as lifting and lowering **heavy** loads, goods on pallets, mesh crates and for height adjustment when materials are being transferred to machines. Ergonomic working due to stepless hydraulic height adjustment. Reliable and safe operation by push button with the functions on/off in a dead man's circuit and emergency stop. Overload protection by integral pressure limitation valve. Optimum safety in operation and maintenance due to integral pipe failure valve and maintenance spigots.

#### Standard:

**DIN EN 1570-1; EG-Maschinenrichtlinie 2006/42/EG und UVV-Vorschriften.**

#### Note:

- **Ambient indoor temperature range of 0 °C to 40 °C.**
- **Before commissioning, the installation and electrical connections should be checked by an expert.**
- **Check the existing load-bearing characteristics of the ground in relation to the overall weight of the lift table.**

### Technical description

Width	800 mm
-------	--------

Safe working load	3000 kg
Weight	320 kg
Overall height C	220 mm
Lift height H	800 mm
Lift time	26 s
Length L	1300 mm
AC supply voltage	400 V
Mains frequency	50 Hz
Power supply	Mains operated
Type of product	Scissor lift table