

ejendals

Pair of gloves, unlined Tegera® 6614, Glove size: 10



Order data

Order number	094386 10
GTIN	7340118315867
Item class	04R

Description

Version:

Tegera® 6614. Leather gloves made of **full-grain leather** for fine mechanical work. Resistant to **contact heat up to 100 °C**. With **oil- and water-repellent coating** on the palm interior.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	10
Type of glove	Driver's gloves
Protection category	Category II
Contents	6
Backing material	Nappa palm leather
Coating variant	No coating

Material	Nappa palm leather
Contact heat up to	100 °C
EN 388	3011X
EN 407	X1XXXX
Application	reusable
Application range	All-round
Colour	black / grey
Type of product	Cowhide split leather gloves