

## ejendals

### Pair of welder's safety gloves Tegera® 118a, Glove size: 11



#### Order data

Order number	094127 11
GTIN	7340118312743
Item class	04R

#### Description

##### Version:

**Tegera® 118a. Allround welder's gloves** made of split-grain cowhide and full-grain goatskin. With **reinforced index finger**. Resistant to **contact heat up to 100 °C**. Unlined.

##### Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

#### Technical description

Glove size	11
Protection category	Category III
Type of glove	Welder's gloves
Glove characteristics	Flame resistance stage 4
Application	reusable
Length	310 mm
Backing material	Full-grain goatskin leather, split-grain cow leather

Coating variant	No coating
Contents	12
Material	Full grain goatskin, split-grain cowhide
Application range	All-round
Application range	Heavy Duty
Contact heat up to	100 °C
EN 388	3121X
EN 407	412X4X
EN 12477	Type B
Welding processes	MIG/MAG
Colour	yellow / white
Standard	EN 407
Type of product	Welder's gloves