

## ejendals

### Pair of welder's safety gloves Tegera® 11CVA, Glove size: 11



#### Order data

Order number	094125 11
GTIN	7340118312668
Item class	04R

#### Description

**Version:**

**Tegera® 11 CVA. Water-repellent allround welder's gloves** made of high-quality full-grain goatskin. With reinforced seams and cuffs. Resistant to **contact heat up to 100 °C**.  
Chromate-free.

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

#### Technical description

Glove size	11
Protection category	Category III
Type of glove	Welder's gloves
Glove characteristics	Flame resistance stage 4
Application	reusable
Length	320 mm
Backing material	Full-grain goatskin

Coating variant	No coating
Contents	12
Material	Full-grain goatskin
Application range	Heavy Duty
Contact heat up to	100 °C
EN 388	3121X
EN 407	412X4X
EN 12477	Type B
Welding processes	WIG
Colour	yellow / white
Standard	EN 407
Type of product	Welder's gloves