

ejendals

Pair of welder's safety gloves Tegera® 11CVA, Glove size: 10



Order data

| | |
|--------------|---------------|
| Order number | 094125 10 |
| GTIN | 7340118312637 |
| Item class | 04R |

Description

Version:

Tegera® 11 CVA. Water-repellent allround welder's gloves made of high-quality full-grain goatskin. With reinforced seams and cuffs. Resistant to **contact heat up to 100 °C**. Chromate-free.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

| | |
|-----------------------|--------------------------|
| Glove size | 10 |
| Protection category | Category III |
| Type of glove | Welder's gloves |
| Glove characteristics | Flame resistance stage 4 |
| Application | reusable |
| Length | 320 mm |
| Backing material | Full-grain goatskin |

| | |
|--------------------|---------------------|
| Coating variant | No coating |
| Contents | 12 |
| Material | Full-grain goatskin |
| Application range | Heavy Duty |
| Contact heat up to | 100 °C |
| EN 388 | 3121X |
| EN 407 | 412X4X |
| EN 12477 | Type B |
| Welding processes | WIG |
| Colour | yellow / white |
| Standard | EN 407 |
| Type of product | Welder's gloves |