

**Garant**
**Open ended spanner / ratchet ring spanner, Width across flats: 32mm**

**Order data**

Order number	614800 32
GTIN	4045197286093
Item class	61B

**Description**
**Version:**

Drop forged. Ring end with especially smooth-running reversible ring ratchet. Extremely small working arc of 5°.

**Material:**

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 425 mm

Jaw width b: 65 mm

Jaw height  $h_1$ : 13.8 mm

Ring thickness  $h_2$ : 17 mm

Ring  $\varnothing$  D: 60 mm

Ratchet torque rating: 900 N·m

**Technical description**

Ratchet torque rating	900 N·m
Ring thickness $h_2$	17 mm
Jaw height $h_1$	13.8 mm
Spanner length L	425 mm
Width across flats	32 mm
Ring $\varnothing$ D	60 mm
Jaw width b	65 mm
Width across flats	metric
Ring setting	0°

No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner