

**Garant**
**Spanner / ratchet ring spanner, Width across flats: 17 mm**

**Order data**

Order number	614800 17
GTIN	4045197160270
Item class	61B

**Description**
**Version:**

Drop forged. Ring end with especially smooth-running reversible ring ratchet. Extremely small working arc of 5°.

**Material:**

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 233 mm

Jaw width b: 36.6 mm

Jaw height  $h_1$ : 7.9 mm

Ring thickness  $h_2$ : 10.9 mm

Ring  $\varnothing$  D: 33.3 mm

Ratchet torque rating: 270 Nm

**Technical description**

Width across flats	17 mm
Spanner length L	233 mm
Jaw height $h_1$	7.9 mm
Ring $\varnothing$ D	33.3 mm
Jaw width b	36.6 mm
Ring thickness $h_2$	10.9 mm
Ratchet torque rating	270 Nm
Width across flats	metric
Ring setting	0 degrees

No. of teeth	72
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner