

**LESSMANN®**  
THE GERMAN BRUSH COMPANY
**Knotted end brush Steel wire, Brush Ø D1× bristle thickness: 22X0,25mm**

**Order data**

Order number	574800 22X0,25
GTIN	4017359019245
Item class	57L

**Description**
**Version:**

Smooth, knotted wire, crimped into steel ferrule, **shank Ø 6 mm**, even density, extremely wear-resistant.

**Application:**

For deburring, removing paint, and for all moderate to heavy brushing jobs. **As speed increases the brush opens, this allows it to be introduced even into tight spaces**, e.g. when brushing the inside of casings.

**Technical description**

Number of twisted knots	8
Brush Ø D <sub>1</sub>	22 mm
maximum speed	20000 min <sup>-1</sup>
Bristle thickness	0.25 mm
Length of brush section H <sub>1</sub>	28 mm
Shank Ø D <sub>s</sub>	6 mm
Brush material	Steel wire
Twisted knotting	left-hand plait
Type of product	End brush

