



Pair of gloves KryTech 580, Glove size: 8



Order data

Order number	094468 8
GTIN	3245425804186
Item class	06D

Description

Version:

KryTech 580 Grip&Proof. For precision work in oily and dirty working conditions. Effective grip in oily and greasy areas due to the **Grip&Proof** technology. Long service life by oil resistance and washable material. Particularly suitable for the machining of workpieces with cutting oil, handling oily metal sheets and machine parts and cutting, stamping and embossing work.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	8
Type of glove	Multi-purpose gloves
Protection category	Category II
Contents	45

Glove characteristics	DMF-free
Glove characteristics	free of latex
Clothing standard	Oeko-Tex Standard 100
EN 388	4342B
Backing material	PEHD
Coating	Nitrile
Coating variant	The palms of the hands
Application range	Precision
Colour	black / grey
Length	230 - 280 mm
Application	reusable
Cut protection class	B
Type of product	Cut-resistant gloves