



Electronics side cutter Super Knips®, conductive grips, kW, overall length: 140mm



Order data

Order number	726660 140
GTIN	4003773081708
Item class	73F

Description

Version:

Slim head with precision ground cutter, without chamfer. Handles with multi-component covering, with opening spring. **Suitable for ESDs.**

Application:

Suitable even for cutting glass fibre cable (fibre optic cable).

Material:

Special tool steel, burnished.

Technical description

Cutting capacity medium-hard steel wire	0.2 - 1.4 mm
overall length	140 mm
Cutter length	12.3 mm
Head width	15.7 mm
Cutting capacity copper wire up to Ø	0.2 - 2.1 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	without bevel
Material	Special quality tool steel, oil-hardened
Standard	DIN ISO 9654
Handle	Multi-component covering

Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Surface	black burnished
Product name attribute	kW
with return spring	yes
with wire holder	no
Type of product	Cutting pliers