



## Electronics side cutter Super Knips<sup>®</sup>, conductive grips, kW, overall length: 140mm



### Order data

Order number	726655 140
GTIN	4003773081661
Item class	73F

### Description

#### Version:

Slim head with precision ground cutter, without chamfer. Handles with multi-component covering, with opening spring. **Suitable for ESDs.**

#### Material:

Made of stainless steel (INOX).

### Technical description

overall length	140 mm
Cutter length	12.3 mm
Cutting capacity medium-hard steel wire	0.2 - 1.2 mm
Head width	15.7 mm
Cutting capacity copper wire up to Ø	0.2 - 2.1 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	without bevel
Material	Stainless steel, INOX
Standard	DIN ISO 9654
Handle	Multi-component covering

Manufacturing process	Cutting edges induction hardened (approx. 54 HRC)
Product name attribute	kW
with return spring	yes
with wire holder	no
Type of product	Cutting pliers