

ejendals

Pair of cold protection gloves Tegera® 296, Glove size: 7



Order data

Order number	094822 7
GTIN	7392626062641
Item class	04R

Description

Version:

Tegera® 296. Lined cold protection gloves of full-grain cowhide leather with **wind-proof and waterproof backs**. The **extra long version** ensures a high thermal insulation and pleasant sensation when wearing. Inner lining of **Thinsulate® material**. With reinforced fingers.

Version of the advertising text:

Tegera® 296. Lined cold protection gloves of full-grain cowhide leather with **wind-proof and waterproof backs**. The **extra long version** ensures a high thermal insulation and pleasant sensation when wearing. Inner lining of **Thinsulate® material**. With reinforced fingers.

Application:

For windy, cold or wet working environments.

Use of the advertising text:

For windy, cold or wet working conditions.

Standard:

EN 388; EN 511

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Note re advertising text:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	7
Protection category	Category II
Type of glove	Cold protection gloves
Contents	6
Application	reusable
Application range	Heavy Duty
Application range	All-round
Standard	EN 511
Length	255 mm
AQL	0.7
EN 388	2122X
EN 511	231
Backing material	Full-grain cowhide leather
Coating	Neoprene
Coating variant	No coating
Colour	white / black
Type of product	Cold protection gloves