

ejendals

Pair of gloves Tegera® 450, Glove size: 11



Order data

| | |
|--------------|---------------|
| Order number | 094562 11 |
| GTIN | 7392626073296 |
| Item class | 04R |

Description

Version:

Tegera® 450. Robust gloves with grip pattern made of nitrile foam for a secure grip on oily components with high cut risk. Ideal for use under **harsh operating conditions** in dirty environments. CRF technology for very high sensitivity.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

| | |
|---------------------|----------------------|
| Glove size | 11 |
| Protection category | Category II |
| Type of glove | Cut-resistant gloves |
| Contents | 12 |
| Knitted technology | 13G |

| | |
|----------------------|------------------------|
| EN 388 | 4X44C |
| Backing material | Nylon, glass fibre |
| Coating | Nitrile foam |
| Coating variant | The palms of the hands |
| Application range | All-round |
| Colour | black |
| Contact heat up to | 100 °C |
| Length | 220 mm |
| Application | reusable |
| Cut protection class | C |
| Type of product | Cut-resistant gloves |