

LESSMANN®
THE GERMAN BRUSH COMPANY
Knotted end brush Steel wire, Brush Ø D₁ × bristle thickness: 22X0,35mm

Order data

Order number	574800 22X0,35
GTIN	4017359014400
Item class	57L

Description
Version:

Smooth, knotted wire, crimped into steel ferrule, **shank Ø 6 mm**, even density, extremely wear-resistant.

Application:

For deburring, removing paint, and for all moderate to heavy brushing jobs. **As speed increases the brush opens, this allows it to be introduced even into tight spaces**, e.g. when brushing the inside of casings.

Technical description

Length of brush section H ₁	28 mm
Number of twisted knots	8
Bristle thickness	0.35 mm
Brush Ø D ₁	22 mm
maximum speed	20000 min ⁻¹
Shank Ø D _s	6 mm
Brush material	Steel wire
Twisted knotting	left-hand plait
Type of product	End brush

