

**Diamond sheet, Grit: D64µm****Order data**

Order number	529110 D64
GTIN	4007220806371
Item class	53B

**Description****Version:**

Flexible diamond sheet, coated **on both sides** with abrasive diamond grit. Height including grit 0.7 mm.

**Application:**

Ideal for grinding work on concave and convex surfaces.

**Note:**

Diamond files can be cleaned in petrol with a metal brush (e.g. 576000).

**Technical description**

Grit	D64
Grit designation	fine
Dimensions	35×350 mm
Grinding media	Diamond
Grinding medium code	D
Width	30 mm
Height	0.7 mm
Length	170 mm
Type of product	Diamond file

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
Carbide (HM)	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
Plastic, GRP	suitable		
Stone	suitable only under restricted conditions		