

**Diamond mini-file Grit D126 (medium) general-purpose, Type: 1****Order data**

Order number	529420 1
GTIN	4007220257029
Item class	53B

Description**Version:**

The blanks are evenly coated with diamond powder and electro-bonded in place. Shorter, more compact design in comparison to diamond needle files. Shank \varnothing 3 mm.

Application:

For precise rework with **compressed air filing devices** (no. 079708) or manual use (quick-release handle no. 519700).

Note:

Other versions on request.

Technical description

Cross-section with coating	5x2 mm
Shape description	flat plain
Coating length	25 mm
Shank \varnothing	3 mm
Coating	double-sided
Overall length	60 mm
Grinding media	Diamond
Grinding medium code	D
Grit	D126
incl. file handle	no
Type of product	Needle file

User data

	Suitability	V_c	ISO code
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
Carbide (HM)	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
Plastic, GRP	suitable		
Stone	suitable only under restricted conditions		