

**Diamond mini-file Grit D126 (medium) general-purpose, Type: 1K****Order data**

Order number	529420 1K
GTIN	4007220665879
Item class	53B

**Description****Version:**

The blanks are evenly coated with diamond powder and electro-bonded in place. Shorter, more compact design in comparison to diamond needle files. Shank  $\varnothing$  3 mm.

**Application:**

For precise rework with **compressed air filing devices** (no. 079708) or manual use (quick-release handle no. 519700).

**Note:**

Other versions on request.

**Technical description**

Cross-section with coating	6.3×1 mm
Shape description	flat tapered
Coating length	16 mm
Shank $\varnothing$	3 mm
Coating	complete
Overall length	55 mm
Grinding media	Diamond
Grinding medium code	D
Grit	D126
incl. file handle	no
Type of product	Needle file

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
Carbide (HM)	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
Plastic, GRP	suitable		
Stone	suitable only under restricted conditions		