

Garant
Open ended spanner / ratchet ring spanner, Width across flats: 10mm

Order data

Order number	614800 10
GTIN	4045197160201
Item class	61B

Description
Version:

Drop forged. Ring end with especially smooth-running reversible ring ratchet. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 160 mm

Jaw width b: 22 mm

Jaw height h_1 : 5.2 mm

Ring thickness h_2 : 7.7 mm

Ring \varnothing D: 20.8 mm

Ratchet torque rating: 70 N·m

Technical description

Ring \varnothing D	20.8 mm
Ratchet torque rating	70 N·m
Spanner length L	160 mm
Jaw width b	22 mm
Ring thickness h_2	7.7 mm
Width across flats	10 mm
Jaw height h_1	5.2 mm
Width across flats	metric
Ring setting	0°

No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner

Accessories

Adapter for ratchet ring spanner Type 1	614850 1
---	----------