

Garant
Open ended spanner / ratchet ring spanner, Width across flats: 38mm

Order data

Order number	614800 38
GTIN	4045197511867
Item class	61B

Description
Version:

Drop forged. Ring end with especially smooth-running reversible ring ratchet. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 482 mm

Jaw width b: 76.2 mm

Jaw height h_1 : 16.6 mm

Ring thickness h_2 : 19.6 mm

Ring \varnothing D: 65.5 mm

Ratchet torque rating: 1150 N·m

Technical description

Jaw height h_1	16.6 mm
Spanner length L	482 mm
Ring \varnothing D	65.5 mm
Width across flats	38 mm
Jaw width b	76.2 mm
Ratchet torque rating	1150 N·m
Ring thickness h_2	19.6 mm
Width across flats	metric
Ring setting	0°

No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner