

**Garant**
**Spanner / ratchet ring spanner, Width across flats: 11 mm**

**Order data**

Order number	614800 11
GTIN	4045197160218
Item class	61B

**Description**
**Version:**

Drop forged. Ring end with especially smooth–running reversible ring ratchet. Extremely small working arc of 5°.

**Material:**

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 168 mm

Jaw width b: 24 mm

Jaw height  $h_1$ : 5.3 mm

Ring thickness  $h_2$ : 8.3 mm

Ring  $\varnothing$  D: 22.5 mm

Ratchet torque rating: 80 Nm

**Technical description**

Width across flats	11 mm
Ring thickness $h_2$	8.3 mm
Ring $\varnothing$ D	22.5 mm
Jaw width b	24 mm
Spanner length L	168 mm
Jaw height $h_1$	5.3 mm
Ratchet torque rating	80 Nm
Width across flats	metric
Ring setting	0 degrees

No. of teeth	72
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner