

LESSMANN®
THE GERMAN BRUSH COMPANY
Knotted end brush Steel wire, Brush Ø D1× bristle thickness: 28X0,50mm

Order data

| | |
|--------------|----------------|
| Order number | 574800 28X0,50 |
| GTIN | 4017359014394 |
| Item class | 57L |

Description
Version:

Smooth, knotted wire, crimped into steel ferrule, **shank Ø 6 mm**, even density, extremely wear-resistant.

Application:

For deburring, removing paint, and for all moderate to heavy brushing jobs. **As speed increases the brush opens, this allows it to be introduced even into tight spaces**, e.g. when brushing the inside of casings.

Technical description

| | |
|--|-------------------------|
| Number of twisted knots | 12 |
| maximum speed | 20000 min ⁻¹ |
| Length of brush section H ₁ | 28 mm |
| Brush Ø D ₁ | 28 mm |
| Bristle thickness | 0.5 mm |
| Shank Ø D _s | 6 mm |
| Brush material | Steel wire |
| Twisted knotting | left-hand plait |
| Type of product | End brush |

