

LESSMANN
THE GERMAN BRUSH COMPANY**End brush Stainless steel wire 0.30 mm, Type: 10X80****Order data**

Order number	574600 10X80
GTIN	4017359006955
Item class	57L

Description**Version:**

Waved special high quality wire, crimped into steel ferrule, **shank Ø 6 mm.**

Application:

For straight die grinders, on flexible drive machines and drills. For cleaning and deburring at inaccessible places.

Technical description

Clamp length L_2	80 mm
Brush Ø D_1	12 mm
maximum speed	15000 min ⁻¹
Clamp Ø D_2	10 mm
Length of brush section H_1	20 mm
Overall length L	120 mm
Type of product	End brush