

Garant**Combination spanner, long version, Width across flats: 20mm****Order data**

Order number	614700 20
GTIN	4045197160058
Item class	61A

Description**Version:**

Drop-forged. With close tolerance jaw width.

With easy-grip profile shaft. Exceptional tool life and wear resistance. **Ring end deep cranked.**

Standard:

DIN 3113 B / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, non-flaking, matt chrome-plated.

Note:

HT-Drive – the special profile. An extremely accurately fitting profile - developed for aviation and aerospace. Tools with this profile can be recognised by the **HT-Drive** symbol. **Advantages:**

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

Technical description

maximum jaw height h1	9 mm
Spanner length L	280 mm
Width across flats	20 mm
Width across flats	metric
maximum ring height h _{2 max}	13.1 mm
Ring setting	15 degrees
Manufacturing process	drop forged

Material	Chrome alloy steel
Surface	chrome-plated over nickel
Type of product	Spanner