

Garant
Open ended spanner / ratchet ring spanner, Width across flats: 27mm

Order data

Order number	614800 27
GTIN	4045197286079
Item class	61B

Description
Version:

Drop forged. Ring end with especially smooth-running reversible ring ratchet. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 359 mm

Jaw width b: 55.2 mm

Jaw height h_1 : 12.5 mm

Ring thickness h_2 : 15 mm

Ring \varnothing D: 52 mm

Ratchet torque rating: 670 N·m

Technical description

Ring \varnothing D	52 mm
Spanner length L	359 mm
Ratchet torque rating	670 N·m
Ring thickness h_2	15 mm
Jaw height h_1	12.5 mm
Width across flats	27 mm
Jaw width b	55.2 mm
Width across flats	metric
Ring setting	0°

No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner