

**Digital caliper IP67, Measuring range: 300mm****Order data**

Order number	412733 300
GTIN	4059192058302
Item class	43A

Description**Version:**

Clearly legible, high-contrast LCD display. Inductive, waterproof measuring system. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. The measuring faces are precision-lapped. Without depth gauge.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032

Technical description

Standard	ISO 13385
Scale divisions	0.0005 in
Scale divisions	0.01 mm
Jaw length	64 mm
Calibration	A1
Measured value saving	MAHR Reference Lock system
Reversible reading	mm / inch
Measuring range	0 - 300 mm

Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement deviation E MPE	± 0.04 mm
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300
DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300

Accessories

Plastic case Type MS300	412470 MS300
Button cell / special battery Battery type CR2032	081560 CR2032