

Garant
Combination spanner set, long version, Number of keys: 14

Order data

Order number	614710 14
GTIN	4045197160164
Item class	61A

Description
Version:

Drop-forged. With close tolerance jaw width.

With easy-grip profile shaft. Exceptional tool life and wear resistance. **Ring end deep cranked.**

Standard:

DIN 3113 B / ISO 3318 / ISO 7738

Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

Supplied with:

1 each combination spanner No. 614700 / 614200 / 614900: Size 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 20; 21; 22; 24

Note:

AS-Drive – the special profile. An extremely accurately fitting profile - developed for aviation and aerospace. Tools with this profile can be recognised by the **AS-Drive** symbol. **Advantages:**

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

Technical description

Number of keys	14
Width across flats	metric

Type of product

Spanner

Accessories

Combination spanner, long version Width across flats 11 mm

614700 11

Combination spanner, long version Width across flats 16 mm

614700 16

Combination spanner, long version Width across flats 10 mm

614700 10

Combination spanner, long version Width across flats 17 mm

614700 17

Combination spanner, long version Width across flats 24 mm

614700 24

Combination spanner, long version Width across flats 19 mm

614700 19

Combination spanner, long version Width across flats 14 mm

614700 14

Combination spanner, long version Width across flats 22 mm

614700 22

Combination spanner, long version Width across flats 15 mm

614700 15

Combination spanner, long version Width across flats 12 mm

614700 12

Combination spanner, long version Width across flats 18 mm

614700 18

Combination spanner, long version Width across flats 13 mm

614700 13

Combination spanner, long version Width across flats 21 mm

614700 21

Combination spanner, long version Width across flats 20 mm

614700 20