

3M**Velour-backed abrasive disc (CER) Hookit 775L Multiple holes, Ø 125 mm, Grit: 120****Order data**

| | |
|--------------|----------------|
| Order number | 567791 120 |
| GTIN | 30051125868236 |
| Item class | 53M |

Description**Version:**

With **stable film backing**. Dust-repellent coating prevents premature clogging.

Advantage:

- **More uniform surface finish due to outstanding grit support.**
- **Improved tear resistance when the edges are stressed.**

Application:

Can be used wet or dry on wood, paint, metal and plastic surfaces.

Cubitron™ II precision grit with the advantage of **quicker material removal** and **more consistent surface finish** on large areas (sheet metal work).

Technical description

| | |
|----------------------------|-------------|
| Grit | 120 |
| Manufacturer's designation | Hookit 775L |
| Disc Ø | 125 mm |
| Series | 775L |

| | |
|---|-----------------------------|
| Grinding media | Cubitron™ II |
| Grinding medium code | Ceramic |
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Product name attribute | Ø 125 mm |
| maximum circumferential speed | 40 m/s |
| Type of product | Velour-backed abrasive disc |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable only under restricted conditions | | |
| INOX | suitable only under restricted conditions | | |
| Ti | suitable only under restricted conditions | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| Paint | suitable | | |
| Uni | suitable | | |
| wet maximum | suitable | | |
| dry | suitable | | |

Accessories

Multi-hole PU backing pad External Ø 123 mm

567990 123