


**3M**
**Velour-backed abrasive disc (A) Hookit 255P 15 holes, Ø 150 mm, Grit: 240**

**Order data**

Order number	567565 240
GTIN	4046719191956
Item class	53M

**Description**
**Version:**

Velour-backed abrasive disc with **paper backing**. Dust-repellent coating prevents premature clogging. The back is covered with hooks and loops.

Velour-backed abrasive disc **Hookit 255P** with open distribution. Aluminium oxide (A) on a C paper base. Ideally suited to materials that have a high tendency to clogging.

**Application:**

On **orbital sanders** with hook and loop pads e.g.No. 567990 (dust extraction available).

Universal **all-round product** for coarse, intermediate and fine abrasion on all metal and plastic surfaces, paint systems and woods.

maximum circumferential speed: 40 m/s

**Technical description**

Disc Ø	150 mm
Manufacturer's designation	Hookit 255P
Grit	240
Grinding media	Aluminium Oxide grit (A)

Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 150 mm
Number of dust extraction holes	15
maximum circumferential speed	40 m/s

---

## Accessories

PU support disc External Ø 150 mm	567885 150
Multi-hole PU backing pad Mounting 5/16 inch and M8 Outer Ø 150 mm	567887 150
Multi-hole PU backing pad Mounting 5/16 inch and M8 External Ø 147 mm	567990 147