

**3M****Velour-backed abrasive disc (CER) Hookit 775L Multiple holes, Ø 125 mm, Grit: 180****Order data**

Order number	567791 180
GTIN	30076308642649
Item class	53M

**Description****Version:**

With **stable film backing**. Dust-repellent coating prevents premature clogging.

**Advantage:**

- **More uniform surface finish due to outstanding grit support.**
- **Improved tear resistance when the edges are stressed.**

**Application:**

Can be used wet or dry on wood, paint, metal and plastic surfaces.

**Cubitron™ II** precision grit with the advantage of **quicker material removal** and **more consistent surface finish** on large areas (sheet metal work).

**Technical description**

Manufacturer's designation	Hookit 775L
Grit	180
Disc Ø	125 mm
Series	775L

Grinding media	Cubitron™ II
Grinding medium code	Ceramic
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 125 mm
maximum circumferential speed	40 m/s
Type of product	Velour-backed abrasive disc

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		
wet maximum	suitable		
dry	suitable		

## Accessories

Multi-hole PU backing pad External Ø 123 mm

567990 123