



## Digital groove depth gauge IP 67, i-wi, Measuring range: 200mm



### Order data

Order number	418754 200
GTIN	4059192057329
Item class	43A

### Description

#### Version:

For measuring cut-outs, grooves, recesses, shoulders etc.  
 Very large LCD display with 11 mm character height. Integral i-wi wireless data interface.  
 Measuring beam with double hook. Both contact faces in a single plane.

#### Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

1 battery No. 081560 size CR2032.

#### Optional extras:

Data cable No. 498940.

i-wi radio receiver No. 498912.

### Technical description

Measuring range	0 - 200 mm
Reversible reading	0.0005 in
Calibration	A2
Reversible reading	mm / inch
Cross-section measuring beam	11.5 × 3.6 mm
Bridge length	100 mm
Reversible reading	0.01 mm

Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
IP Index of Protection	IP 67
Power supply	Battery-powered
Wireless application	Manufacturer's software
Measurement deviation E MPE	$\pm 0.03$ mm
Standard	ISO 13385
Interface	Digimatic interface
Interface	USB interface
Interface	RS232C interface
Interface	MAHR i-wi radio system
Measured value saving	MAHR Reference Lock system
Measurement technology	digital
Material	Stainless steel, INOX
Packaging	sturdy box
Type of product	Groove depth gauge

## Services

Calibration Vernier hook depth gauge maximum measuring range 200 mm	021220 200
DAkkS calibration Vernier hook depth gauge maximum measuring range 200 mm	021230 200

## Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Radio receiver for Mahr i-wi Type STICK	498914 STICK
Radio receivers for Mahr i-wi Type STICK	498912 STICK
Multi-receiver / USB keyboard interface Type	498975