

LESSMANN®
THE GERMAN BRUSH COMPANY

Dished bevel brush Stainless steel wire 0.50 mm, Brush Ø D1× thread M: 125XM14mm



Order data

Order number	571350 125XM14
GTIN	4017359391945
Item class	57L

Description

Version:

Dished **bevel brush** with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body.
Very aggressive brushing effect with high wear resistance.

Application:

Left knotted, reliably avoids premature unwinding.

Ideal for working where access is difficult and for heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

With **internal thread M14**, for direct mounting **on angle grinders**.

Technical description

maximum speed	12500 min ⁻¹
Length of brush section H ₁	29 mm
Brush Ø D ₁	125 mm
Number of twisted knots	20

Bristle thickness	0.5 mm
Bristle width L ₁	12 mm
Thread M	M14
Brush material	Stainless steel wire
Twisted knotting	left knotted
Type of product	Bevel brush