



## Work trousers CANVAS 320, black, Clothing size DE: 24



### Order data

Order number	091362 24
GTIN	4030913039763
Item class	09R

### Description

#### Version:

Robust **work clothing line canvas 320** offers high protection for a wide variety of working conditions. With **elasticated waistband** for a comfortable fit. Tear-resistant and abrasion resistant due to **Cordura® reinforcement** at particularly stressed areas. Thanks to the Teflon® reinforcement, the easy-care fabric is **dirt-repellent and water-repellent**. With reflective piping of **3M™ Scotchlite™ reflective material** for better visibility in the dark.

**Work trousers** with seven belt loops.

- **Cordura® reinforced knee padding pockets.**
- **Certified to EN-14404 together with knee padding.**
- **Reinforced back pockets.**
- **Two side pockets of Cordura®.**
- **Double ruler pocket of Cordura®.**
- **Thigh pocket with patch mobile phone pocket.**
- **Zip fastener flies.**

#### Note:

This sizes listed in the shop are the DE clothing sizes. Please see the size table or the technical data for the corresponding sizes for your country.

Available in other colours on request.

Size table showing equivalent international sizes can be found on our overview page.

Fabric composition: 65% polyester

Fabric composition: 35% cotton  
 Material weight/fabric density: 320 g/m<sup>2</sup>  
 Washing: 60 °C coloureds

## Technical description

Size FR	44C
Size IT	44C
Clothing size DE	24
Series	CANVAS 320
Special service provision	Textile finishing
Size ES	44C
Gender	Gentlemen's
Fabric composition	65% polyester
Fabric composition	35% cotton
Material weight/fabric density	320 g/m <sup>2</sup>
Washing	60 °C coloureds
Bleaching	do not bleach
Dry-cleaning	Cleaning with perchlorethylene
Drying	gentle tumble drying (low temperature)
Ironing	moderately hot, up to maximum 150 °C
Colour	black
Type of product	Work trousers