

Garant
Open ended spanner / ratchet ring spanner with swivel head, Width across flats: 16mm

Order data

Order number	614812 16
GTIN	4045197160447
Item class	61B

Description
Version:

Drop forged. Ring end with especially smooth-running reversible ring ratchet. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 216 mm

Jaw width b: 34 mm

Jaw height h_1 : 7.1 mm

Ring thickness h_2 : 10.6 mm

Ring \varnothing D: 30.3 mm

Ratchet torque rating: 250 N·m

Technical description

Jaw width b	34 mm
Ring \varnothing D	30.3 mm
Ratchet torque rating	250 N·m
Ring thickness h_2	10.6 mm
Width across flats	16 mm
Jaw height h_1	7.1 mm
Spanner length L	216 mm
Width across flats	metric

No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner