



## Bi-hexagon socket, 1/2 inch, Width across flats: 25mm



### Order data

Order number	642100 25
GTIN	4018754005338
Item class	63A

### Description

#### Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads. Square socket drive with close tolerances for secure fit on the drive attachment. Internal square to **DIN 3120**. Optimum grain orientation due to special forging process. Close tolerance width across flats. No rounding of bolt corners, nuts and bolt heads are protected. Hardened in an oil bath, stress-relieved and distortion-free for a precision fit. Smoothed finish. **AS drive** profile.

#### Standard:

**DIN 3124**

#### Material:

HPQ® high performance steel, non-flaking chrome-plated over nickel.

#### Note:

**PLEASE NOTE!**

An alternative from GARANT is also available for this product.

Recommended product number: 642129

### Technical description

Ø drive output end	33.2 mm
Length	42 mm
Width across flats	25 mm
Square drive	1/2 in

Standard	DIN 3124
Drive profile	Bi-hex socket
Material	HPQ® high performance steel
Surface	chromium-plated over nickel
with AS Drive profile.	yes
Type of product	Socket insert