



Bi-hexagon socket, 1/2 inch, Width across flats: 26mm



Order data

Order number	642100 26
GTIN	4018754005345
Item class	63A

Description

Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads. Square socket drive with close tolerances for secure fit on the drive attachment. Internal square to **DIN 3120**. Optimum grain orientation due to special forging process. Close tolerance width across flats. No rounding of bolt corners, nuts and bolt heads are protected. Hardened in an oil bath, stress-relieved and distortion-free for a precision fit. Smoothed finish. **AS drive** profile.

Standard:

DIN 3124

Material:

HPQ® high performance steel, non-flaking chrome-plated over nickel.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 642129

Technical description

Length	42 mm
Width across flats	26 mm
Ø drive output end	34.4 mm
Square drive	1/2 in

Standard	DIN 3124
Drive profile	Bi-hex socket
Material	HPQ® high performance steel
Surface	chromium-plated over nickel
with AS Drive profile.	yes
Type of product	Socket insert