

**Garant****Double ratchet ring spanner, 15° offset, Jaw widths: 12X13mm****Order data**

Order number	614845 12X13
GTIN	4045197415899
Item class	61B

**Description****Version:**

Drop forged, with particularly free-running sturdy ratchet ring at each end. Reversible for left- and right-hand tightening. Extremely small working arc of 5°.

**Material:**

Chrome vanadium steel, matt chrome-plated.

**Technical description**

overall length L	170 mm
maximum ring $\varnothing$ D2	26.5 mm
Width across flats 2	13 mm
maximum ring $\varnothing$ D1	24.6 mm
Width across flats 1	12 mm
maximum ring height $h_2$	9 mm
maximum ring height $h_1$	8.9 mm
Width across flats	metric
No. of teeth	5
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel

Surface	matt chrome-plated
Type of product	Spanner

---

## Accessories

Adapter for ratchet ring spanner Type 2	614850 2
---	----------