

**HOLEX****Hacksaw frame with handle with bimetel blade 24 teeth****Order data**

Order number	580800
GTIN	4045197377449
Item class	52S

**Description****Version:**

Hacksaw frame with all-steel back. Alternative blade setting at 90° for flush cutting. Plastic handle. Overall length 520 mm.

The bow saw with its prominent bow frame is characterised by the u-shaped bow which tensions the saw blades. The limitation in depth of cut of hand bow saws is presented by the distance from the blade to the bow. This frame shape permits the use of particularly slim saw blades, which in other frame shapes would be liable to buckle when subjected to cutting movements with the force in alternate senses or other than in the pulling sense. Thanks to the thin hacksaw blades the metal cutting effort required is reduced, because of the small cutting width. Thus this type of saw is the classic standard for hacksaw work in metalworking.

**Supplied with:**

HOLEX bimetel hacksaw blade No. 582970.

**Technical description**

TPI	24
Blade length	300 mm
Type of product	Hacksaw frame

**Accessories**

Hacksaw blade, single-sidedbimetal

582970