

Garant**Double ratchet ring spanner, 15° offset, Jaw widths: 16X18mm****Order data**

Order number	614845 16X18
GTIN	4045197416216
Item class	61B

Description**Version:**

Drop forged, with particularly free-running sturdy ratchet ring at each end. Reversible for left- and right-hand tightening. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Technical description

maximum ring height h_2	11 mm
overall length L	230 mm
maximum ring \varnothing D2	35.6 mm
Width across flats 2	18 mm
maximum ring height h_1	9.9 mm
maximum ring \varnothing D1	34.5 mm
Width across flats 1	16 mm
Width across flats	metric
No. of teeth	5
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel

Surface	matt chrome-plated
Type of product	Spanner