

LESSMANN®
THE GERMAN BRUSH COMPANY

Fine scratch brush Waved brass wire 0.15 mm, Type: W



Order data

Order number	576705 W
GTIN	4017359074664
Item class	57L

Description

Version:

Overall length approx. 225 mm, 4 rows, area carrying bristles 110×20 mm, bristle height 20 mm.

Beechwood body

Description:

Fine brushes, also known as watchmaker or goldsmith brushes, are characterised by their high-density bristles. These brushes are frequently used for the application of solvents and cleaning agents. They are available in different widths.

Brass wire brushes are softer than steel wire brushes. Among other things, they are also suitable for handling mild alkalis. Brass wire is mainly required for machining non-ferrous metals.

Application:

High density for fine removal of surface blemishes.

Technical description

Base body material	Beech wood
Overall length L	225 mm
Brush material	Brass, waved
Bristle thickness	0.15 mm
Working length L ₃	110 mm
Length of brush section H ₁	20 mm
Bristle width L ₁	20 mm
Number of rows of bristles	4
Type of product	Fine brush

