


SANDFLEX® mini-hacksaw with 2 saw blades (wood / metal)

Order data

Order number	580950
GTIN	7311518044558
Item class	58Z

Description
Version:

Oval frame made of strong steel tube, with knuckle protection. Including wood rip cut saw blade and bimetal blade. Has a place in every toolbox.

The bow saw with its prominent bow frame is characterised by the u-shaped bow which tensions the saw blades. The limitation in depth of cut of hand bow saws is presented by the distance from the blade to the bow. This frame shape permits the use of particularly slim saw blades, which in other frame shapes would be liable to buckle when subjected to cutting movements with the force in alternate senses or other than in the pulling sense. Thanks to the thin hacksaw blades the metal cutting effort required is reduced, because of the small cutting width. Thus this type of saw is the classic standard for hacksaw work in metalworking.

Application:

Universal for sawing wood, metal (see No. 582500 – 582970) and when using the carbide rod saw No. 582990 also tiles, bricks, cast iron etc. Overall length only 300 mm.

Note:

Spare saw blades for wood, see No. 582985.

Technical description

Overall length	300 mm
Blade length	300 mm
Number of saw blades	2
Type of product	Bow saw

Accessories

Hacksaw blade, single-sidedSANDFLEX®, bimetal	582900
Carbide rod saw blade for tiles, bricks, cast iron etc.	582990
Hacksaw blade, single-sidedbimetal, progressive	582500
Hacksaw blade, single-sidedbimetal	582950
Hacksaw blade, single-sidedSANDFLEX®, bimetal	582850
Hacksaw blade, single-sidedbimetal	582970
Hacksaw blade, single-sidedfor wood	582985
Hacksaw blade, single-sidedSANDFLEX®, bimetal	582920