

LESSMANN[®]
THE GERMAN BRUSH COMPANY**Tube brush Smooth steel wire, Brush Ø: 75mm****Order data**

Order number	578000 75
GTIN	4017359026571
Item class	57L

Description**Version:**

Internal brushes with galvanised twisted wire core and plain helix of bristles. Bristles of smooth steel wire, overall length 160 mm. Brush section 100 mm long with crimped-on 1/2 inch Whitworth thread nipple.

Application:

For cleaning pipes, gratings, sleeves, heat exchangers, and cylinders.

For use in machines (only clockwise rotation), use thread adapter No. 578005.

Suitable for:

Pipe inside Ø [inches]: 3 inch

Technical description

Brush Ø D ₁	75 mm
Type of product	Tube brush

Accessories

Thread adapter for tube brush No. 578000Shank Ø 6 mm	578005
Extension for tube brush No. 578000	578010