



JOKER 6000 open ended spanner / ratchet ring spanner, Width across flats: 10mm



Order data

Order number	614870 10
GTIN	4013288165268
Item class	63F

Description

Version:

Drop forged. Ring end with smooth-running sturdy precision ring ratchet (80 teeth) with a particularly small working arc of 4.5°.

The open end has a bi-hexagon profile and a replaceable hardened metal plate, which fulfils a stop function, preventing slippage and allowing a small working arc.

Material:

Chrome molybdenum steel, matt chrome-plated.

Technical description

Width across flats	10 mm
Spanner length L	159 mm
Ring Ø D	21 mm
Jaw height h ₁	5.5 mm
Ring thickness h ₂	7.2 mm
Jaw width b	22 mm
Width across flats	metric
Manufacturer's designation	6000 Joker
Ring setting	0 degrees
No. of teeth	80
Working arc	4.5 degrees

Manufacturing process	drop forged
Material	Chrome-molybdenum steel.
Surface	matt chrome-plated
Ratchet reversible	no
Type of product	Spanner

Accessories

Adapter for ratchet ring spanner Type 1	614850 1
---	----------