

LESSMANN®
THE GERMAN BRUSH COMPANY

Fine scratch brush Stainless steel wire waved 0.15 mm, Type: P



Order data

| | |
|--------------|---------------|
| Order number | 576805 P |
| GTIN | 4017359350751 |
| Item class | 57L |

Description

Version:

Overall length approx. 225 mm, 4 rows, area carrying bristles 110×20 mm, bristle height 20 mm.

Plastic body, for use in areas with high hygiene requirements.

Application:

High density for fine removal of surface blemishes.

Technical description

| | |
|--|------------------------|
| Base body material | Plastic |
| Overall length L | 225 mm |
| Brush material | Stainless steel, waved |
| Bristle thickness | 0.15 mm |
| Working length L ₃ | 110 mm |
| Length of brush section H ₁ | 20 mm |
| Bristle width L ₁ | 20 mm |
| Number of rows of bristles | 4 |
| Type of product | Fine brush |