

**Combination spanner, long version, Width across flats: 8mm****Order data**

Order number	614900 8
GTIN	4045197442024
Item class	62A

Description**Version:**

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, chrome-plated.

Technical description

maximum jaw height h1	5 mm
Spanner length L	148 mm
Width across flats	8 mm
Width across flats	metric
maximum ring height $h_{2\max}$	7 mm
Ring setting	15 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	chrome-plated
Type of product	Spanner

