



## Double-ended ring spanner set, deeply cranked, Number of keys: 10ZOLL



### Order data

Order number	615500 10ZOLL
GTIN	4018754081165
Item class	63A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Ring end with **AS drive** profile.

#### Standard:

**DIN 838 / ISO 3318**

#### Material:

Chrome vanadium steel, chrome-plated.

#### Supplied with:

1 each double ended ring spanner No. 615600 / 615000 / 615900 / 615950: 1/4×5/16; 3/8×7/16; 1/2× 9/16; 9/16×5/8; 19/32×11/16; 5/8×3/4; 11/16×13/16; 3/4×7/8; 25/32×13/16; 7/8×15/16 inch

### Technical description

Number of keys	10
Width across flats	imperial
Ring setting	75 degrees
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chrome plated (non-flaking)

Type of product

Spanner