



## Combination spanner, long version, Width across flats: 24mm



### Order data

Order number	614900 24
GTIN	4045197442178
Item class	62A

### Description

**Version:**

Drop-forged. With close tolerance jaw width.  
With oval shaft.

**Standard:**

**DIN 3113 A / ISO 3318 / ISO 7738**

**Material:**

Chrome vanadium steel, chrome-plated.

### Technical description

maximum jaw height h1	10.2 mm
Spanner length L	338 mm
Width across flats	24 mm
Width across flats	metric
maximum ring height h <sub>2max</sub>	15.7 mm
Ring setting	15 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	chrome-plated
Type of product	Spanner

