

ELTEN**Lace-up boots grey VINTAGE Mid ESD, S3, EU shoe size: 40****Order data**

Order number	092231 40
GTIN	4030839220542
Item class	09P

Description**Version:**

Modern safety shoes in vintage design.

- **Upper material of sturdy cowhide.**
- **Breathable textile lining, BIOACTIVE for a pleasant foot climate.**
- **Padded tongue.**
- **ESD PRO grey full-size insole.**
- **L10 TPU/PU sole, anti-slip.**
- **ESD security.**

Safety shoe with bioactive inner lining. Particularly **gentle to the skin and odour-suppressant**.

Extra laces supplied (grey).

Standard:

EN ISO 20345:2011 S3 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Supplied with:

With extra laces in grey.

Note:

Stock goods in EU sizes 39 – 46, can be ordered in EU sizes 37 – 48.

electrostatic characteristic: EGB/ESD

Protection class: S3

Material of protective toe-cap: Steel

Puncture resistance: Textile

Standard: Inlay type-tested according to DGUV regulation 191

Technical description

Standard	Inlay type-tested according to DGUV regulation 191
Closure	Laces
Uppers material	Genuine leather
Puncture resistance	Textile
suitable for orthopaedic insoles	yes
against water penetration and water absorption	yes
Material of outer sole	TPU/PU
Protection class	S3
Material inner lining	breathable textile inner lining
Colour	grey
Shoe type	Bootlaces
oil- and petrol-resistant sole	yes
Material of protective toe-cap	Steel
anti-static	yes
EU shoe size	40
Energy absorption in the heel area	yes
contains no metal or leather	no
The entire shoe is waterproof	yes
Series	VINTAGE
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety boots